

BSP Adapter kit includes 7 total parts; 4 adapters, 2 multi-seals and lower piece.

PK-ADPT-DH500/BSP, ADAPTOR KIT, DH500 TO 1/8, 1/4, 3/8, 1/2 BSP FEMALE, pn 3466419

Item Num	Qty	Description	Max, MPa (psi)
3068887	1	NPPL-103974,NIPPLE, 2.75 IN, DH500 (500M)	500 (72500)
3068607	2	CLLR-101201,COLLAR, DH500/DH700 (700M)	700 (100000)
3068419	2	GLND-100271,GLAND, DH500 (400M)	400 (60000)
3499288	1	BSP ADPTR FITTINGS,DH500 TO 1/8, 1/4, 3/8, 1/2 BSP-F	see photo

Note that the adapter fitting is LH thread on bottom and RH thread on top (both are 3/8 BSP). This allows user to keep gauge face straight while tightening.

DH500 collar, gland, 2.75 inch nipple would be used with gauge with high pressure fitting (9/16-18 UNF)

