

Tech Notes

Title: Can the 1586A go up to 100M ohm?

Created: 2-4-14

Last Revised:

Applies To: 1586A


Problem Description: Data sheet states 100M ohm, yet the range is 10M ohm. Which is correct?

Resolution/Work Around: The 100 M-ohm range is available for channel 001 only. From the user manual, pg. 3-20.

③	Set the range to: Auto, 100 Ω, 1 kΩ, 10 kΩ, 100 kΩ, 1 MΩ or 10 MΩ. Ch001 can be set to 100 MΩ.
---	--

This isn't very obvious when reading the specs which is something we can improve.

Below is channel 001 showing the 100 M-ohm range.



Other Information: