



FLUKE[®]

**Process
Instruments**

Fluke Process Instruments

Statement of Calibration Practices

Serial Number: TV36-SA-L-W-60
Model: 62983001
Measurement Temp Range: -10°C to +1300°C (14°F to +2372°F)
not calibrated under -10°C (-4°F)
Accuracy: ±2°C (4°F) or 2% of reading
whichever is greater
Date: 2023-09-26
Certified By: Fluke QA Manager

This calibration is traceable to the International System of Units (SI) through recognized national metrology institutes (NIST, PTB, NPL, NIM, NRC, etc.), radiometric techniques, or natural physical constants. The calibration has been performed in accordance with the Fluke Corporation ISO 9001 Quality Manual, QSD 111.00. This certificate applies to only the item identified and shall not be reproduced except in full, without the specific written approval by Fluke Corporation.