

## Fluke Calibration - Various adapters for pressure calibrations

<b>ADAPTERS:</b>		
<i>1/8" Swagelok:</i>		
ADPTR-100319	3068564	ADAPTOR, 1/8 IN NPTM X 1/8 IN SWGM
ADPTR-101574	3068641	ADAPTOR, 1/4 IN NPTM X 1/8 IN SWGM
ADPTR-400519	3069070	ADAPTOR, DH200F X SWGM, BULKHEAD
ADPTR-400518	3069062	ADAPTOR, DH200M X 1/8 IN SWGM
<i>1/4" Swagelok:</i>		
ADPTR-102033	3068676	ADAPTOR, 1/8 IN NPTM X 1/4 IN SWGM
ADPTR-100109	3068350	ADAPTOR, 1/4 IN NPTM X 1/4 IN SWGM
ADPTR-400528	3069081	ADAPTOR, DH200M X 1/4 IN SWGM
<i>1/8" Male NPT O-Seal:</i>		
ADPTR-400560	3069096	ADAPTOR, DH200F X 1/8 IN NPSM O-SEAL
<i>1/8" Female NPT:</i>		
ADPTR-100299	3068547	ADAPTOR, DH200F X 1/8 IN NPTF
<i>1/8" Male NPT:</i>		
ADPTR-100319	3068564	ADAPTOR, 1/8 IN NPTM X 1/8 IN SWGM
ADPTR-102033	3068676	ADAPTOR, 1/8 IN NPTM X 1/4 IN SWGM
ADPTR-100301	3068558	ADAPTOR, DH200F X 1/8 IN NPTM
ADPTR-102819	3068785	ADAPTOR, DH500F X 1/8 IN NPTM
<i>1/4" Female NPT:</i>		
ADPTR-100297	3068535	ADAPTOR, DH200F X 1/4 IN NPTF
ADPTR-102820	3068797	ADAPTOR, DH500F X 1/4 IN NPTF
<i>1/4" Male NPT:</i>		
ADPTR-101574	3068641	ADAPTOR, 1/4 IN NPTM X 1/8 IN SWGM
ADPTR-100109	3068350	ADAPTOR, 1/4 IN NPTM X 1/4 IN SWGM
ADPTR-100287	3068481	ADAPTOR, DH200F X 1/4 IN NPTM
ADPTR-102889	3068810	ADAPTOR, DH500F X 1/4 NPTM
<i>AN4 Female</i>		
ADPTR-400566	3069118	ADAPTOR, DH200F X AN4F
<i>AN4 Male</i>		
ADPTR-400561	3069107	ADAPTOR, DH200F X AN4M
ADPTR-102888	3068805	ADAPTOR, DH500F X AN4M
<i>DH200 Female</i>		
ADPTR-400560	3069096	ADAPTOR, DH200F X 1/8 IN NPSM O-SEAL
ADPTR-100299	3068547	ADAPTOR, DH200F X 1/8 IN NPTF
ADPTR-100301	3068558	ADAPTOR, DH200F X 1/8 IN NPTM
ADPTR-400519	3069070	ADAPTOR, DH200F X SWGM, BULKHEAD
ADPTR-100297	3068535	ADAPTOR, DH200F X 1/4 IN NPTF
ADPTR-100287	3068481	ADAPTOR, DH200F X 1/4 IN NPTM
ADPTR-400566	3069118	ADAPTOR, DH200F X AN4F
ADPTR-400561	3069107	ADAPTOR, DH200F X AN4M
CRSS-100284	3068462	CROSS, DH200 (140M)
ELBW-100280	3068443	ELBOW, DH200 (140M)

TEE-100282	3068455	TEE, DH200 (140M)
UNION-100293	3068512	UNION, DH200 (140M)
ADPTR-103686	3068831	ADAPTOR, DH500F X DH200-2M M
<b>DH200 Male</b>		
ADPTR-400518	3069062	ADAPTOR, DH200M X 1/8 IN SWGM
ADPTR-400528	3069081	ADAPTOR, DH200M X 1/4 IN SWGM
CLLR-101200	3068599	COLLAR, DH200 (140M)
GLND-100272	3068428	GLAND, DH200 (140M)
NPPL-100205	3068389	NIPPLE, 6 IN, DH200 (140M)
NPPL-100206	3068392	NIPPLE, 12 IN, DH200 (140M)
NPPL-100204	3068377	NIPPLE, 2.75 IN, DH200 (140M)
NPPL-100269	3068404	NIPPLE, 24 IN, DH200 (140M)
PLUG-100279	3068437	PLUG, DH200 (140M)
<b>DH500 Female</b>		
ADPTR-102819	3068785	ADAPTOR, DH500F X 1/8 IN NPTM
ADPTR-102820	3068797	ADAPTOR, DH500F X 1/4 IN NPTF
ADPTR-102889	3068810	ADAPTOR, DH500F X 1/4 NPTM
ADPTR-102888	3068805	ADAPTOR, DH500F X AN4M
ADPTR-103686	3068831	ADAPTOR, DH500F X DH200-2M M
CRSS-100289	3068496	CROSS, DH500 (400M)
ELBW-100168	3068361	ELBOW, DH500 (400M)
TEE-100291	3068501	TEE, DH500 (400M)
UNION-100295	3068520	UNION, DH500 (400M)
FLTR-402376	3071807	FILTER, DH500 X DH500, 40 MIC (400M)
<b>DH500 Male</b>		
CLLR-101201	3068607	COLLAR, DH500/DH700 (700M)
GLND-100271	3068419	GLAND, DH500 (400M)
NPPL-103974	3068887	NIPPLE, 2.75 IN, DH500 (500M)
NPPL-103977	3068916	NIPPLE, 24 IN, DH500 (500M)
NPPL-103975	3068893	NIPPLE, 6 IN, DH500 (500M)
NPPL-103976	3068902	NIPPLE, 12 IN, DH500 (500M)
PLUG-100285	3068470	PLUG, DH500/DH700 (700M)
<b>INTERCONNECTION KITS:</b>		
PK-7600-PPC/MPCDIF	3070127	INTERCONNECT KIT, FOR PG7600 DIFFERENTIAL MODE
PK-7600-VAC-REF	3071834	INTERCONNECT KIT, PLATFORM REF TO VAC PUMP
PK-7600-VAC-VENT	3070854	FAST VENT VACUUM VALVE KIT
PK-7000-PPC/MPC	3069508	INTERCONNECT KIT, PG7000 & CONTROLLER
		Use to connect MPC1, 3990 or PPC4 to PG7XXX and DUT
PK-MPG2-RPM/PG	3367797	INTERCONNECT KIT FOR MPG2-H & RPM/PG7000
PK-E-DWT/UUT	3466377	INTERCONNECT KIT FOR E-DWT TO UNIT UNDER TEST, NO ADAPTORS
PK-PPC-TEST	3069889	INTERCONNECT KIT, 20 MPA, PPC-TEST
		Interconnect, connect PPC4 or PPC4E to DUT with QC
PK-6270-NPT	4456668	LINES AND FITTINGS KIT, 6270A NPT
PK-6270-BSP	4456679	LINES AND FITTINGS KIT, 6270A BSP
PK-6270-7/16	4472019	LINES AND FITTINGS KIT, 6270A 7/16-20
PK-2271A-NPT-HC20	4755295	LINES AND FITTINGS KIT FOR 2271A-NPT-HC20

PK-2271A-BSP-HC20	4755301	LINES AND FITTINGS KIT FOR 2271A-BSP-HC20
PK-2271A-NPT-P3K	4755312	LINES AND FITTINGS KIT FOR 2271A-NPT-P3000
PK-2271A-BSP-P3K	4755320	LINES AND FITTINGS KIT FOR 2271A-BSP-P3000
7000-110	3876298	LINES AND FITTINGS KIT
		connects supply, vacuum and DUT to 7250

**VALVES:**

<i>Vacuum Valves</i>		
VLV-102763	3068760	VALVE, VACUUM SHUTOFF, KF25
<i>Gas Pressure Valves</i>		
VLV-400902-01	3072273	VALVE, 100MPA, GAS, MANUAL
<i>Oil Pressure Valves</i>		
VLV-400902-04	3072300	VALVE, 200MPA, OIL ,MANUAL, ISOLTN, INLET
VLV-400902-02	3072286	VALVE, 200MPA ,OIL, MANUAL,SHUTOFF, OUTLET
VLV-400902-03	3072299	VALVE, 500MPA, OIL, MANUAL